# Temperature Controllers

## Model TEC-8300 1/8 DIN

Out1 Out2 Alm1 Alm2

TEC-8300

0

TEMPCO

Power Input BOX 1

4 = 90-264 VAC 5 = 11-26 VAC / VDC

9 = Other



# Model TEC-8300 1/8 DIN Temperature Controller

### **Design Features**

- \* 1/8 DIN size 48 mm × 96 mm
- \* Fuzzy Logic PID Autotune heat and cool control
- \* Short panel depth only 2-9/16" (65 mm) required
- \* Universal input, field configurable (Type J T/C default, PT100, mA, V) with high accuracy 18-bit D-A
- \* Heater Break Alarm using 0-50 Amp current transformer
- \* Output 2 can be programmed as cooling output only
- \* 2 optional alarms programmable NO or NC relay
- \* Wide variety of alarm mode selections
- \* Bumpless transfer to manual mode during sensor failure
- \* Universal input power, 90-264 VAC
- \* Power limiter output
- \* RS-485 and RS-232 data communications interface

- \* Bright 0.40" (10 mm) red LED process display, 0.31" (8 mm) green LED setpoint display stabilized with a digital filter if required
- \* Fast input sample rate (5 samples/second)
- \* Automatic programming
- \* Differential control
- \* "Soft-Start" ramp and dwell timer
- \* Analog input for remote setpoint and current transformer
- \* Event input for changing functions and setpoint
- \* Hardware lockout plus remote lockout protection
- \* Loop break alarm
- \* Analog retransmission
- \* DC power supply outputs
- \* Tempco's most highly featured 1/8 **DIN** control

# Hardware Code: TEC-8300-

Configurable for

**5** Programmable

**Outputs!** 

Agency Approvals:

File #:

E244198

**Signal Input** — Universal, can be programmed in the field BOX 2

- **1** = Input 1 Universal input (factory default = tc type J) Thermocouple: J, K, T, E, B, R, S, N, L RTD: PT100 DIN, PT100 JIS Current: 4-20 mA, 0-20 mA Voltage: VDC, 0-1, 0-5, 1-5, 0-10
  - Input 2 CT: 0 50A AC current Transformer (factory default) Linear Input: 0-1V, 0-5V, 1-5V, 0-10V, 0-20mA, 4-20mA Input 3 – Event Input
- 9 = Other

### Output 1 BOX 3

- 1 = Relay: 2A / 240 VAC
- 2 = Pulse DC for SSR drive: 5 VDC (30 mA max)
- 3 =Isolated, 4-20 mA (default), 0-20 mA
- **4** = Isolated, VDC, 1-5 (default), 0-5, 0-1 **5** = Isolated, VDC, 0-10
- 6 = Triac-SSR output 1A / 240 VAC
- **C** = Pulse DC for SSR drive: 14 VDC (40 mA max)
- = Other

### Output 2 BOX 4

- $\mathbf{0} = \text{None}$
- **1** = Relay: 2A / 240 VAC
- 2 = Pulse DC for SSR drive: 5 VDC (30 mA max)
- 3 =Isolated, 4-20 mA (default), 0-20 mA
- **4** = Isolated VDC, 1-5 (default), 0-5, 0-1 **5** = Isolated VDC, 0-10
- 6 = Triac-SSR output 1A / 240 VAC
- a Finde Soft Ode and TA (200 MAC)
  b Finde Soft Ode and TA (200 MAC)
  b Finde Soft Ode and TA (200 MAC)
  b Finde Soft Ode and TA (200 MAC)
  c Finde Soft Ode and TA (200 MAC)
  <lic Finde Soft Ode and TA (200 MAC)</li>
- A = Other



A Part Number based on the hardware code and any software pre-programming will be issued at time of order.

Alarm 1 BOX 5  $\mathbf{0} = \text{None}$ 1 = Relay: 2A/240 VAC, SPDT9 = Other

#### Alarm 2 BOX 6

- $\mathbf{0} = \text{None}$
- 1 = Relay: 2A/240 VAC, SPST
- 9 = Other

#### Communications BOX 7

- $\mathbf{0}$  = None
- 1 = RS-485 Interface 2 = RS-232 Interface
- 3 = Retransmission 4-20 mA (default), 0-20 mA
- **4** = Retransmission 1-5 VDC (default), 0-5 VDC 5 = Retransmission 0.10 VDC
- 9 = Other

#### **Transformer for Heater Break Alarm** (0-50 Amp current) Part Number: TEC99999 Specifications on page 13-47

Note: Detailed information on features common to digital microprocessor-based TEC temperature controls and the complete Table of Input Range and Accuracy can be found on page 13-46.

View Product Inventory @ www.tempco.com